



**SPECIFICATIONS:**

RATING: 100V AC 1A MAX  
 12V DC 2A MAX  
 INSULATION RESISTANCE:  
 MIN 50 MEGOHM @ 250V DC  
 VOLTAGE WITHSTAND:  
 250V AC, 1 MINUTE  
 CONTACT RESISTANCE:  
 30 MOHM MAX-PINS  
 50 MOHM MAX-SHELL

**Application Notes:**

Use 26AWG ~ 28AWG Wire  
 Soldering Temp.: 180° C  
 Soldering Time: 0.5 sec. ~ 1.0 sec.

**9615 SW Allen, Suite 103**  
**Beaverton, OR 97005**  
**Phone: (503) 643-4899**  
**800-275-4899**  
**Fax: (503) 372-1266**  
**Website: www.cui.com**



**MODULAR IN LINE RECEPTACLE**

PART NO. MD-90J		UNITS: MM [INCHES]	
DRAWN BY:		APPROVED BY:	
SCALE: 2X			