


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

- UL LISTED AND CSA CERTIFIED FOR:
  - 600V MAX VOLTAGE RATING
  - 221°F (105°C) MAX TEMP RATING
  - STRANDED COPPER WIRE ONLY
  - 6-12 LBS INSERTION/WITHDRAWAL FORCE
- MATERIAL:
  - STAMPING-CDA 260 BRASS, TIN PLATED
  - HOUSING-TYPE 66 NYLON
- DIMENSIONS IN BRACKETS ARE IN mm OR mm<sup>2</sup>
- COLORS ARE TRANSLUCENT
- INSTALLATION TOOLS: CT-300-1
- PACKAGE QTY:
  - STD: C=100
  - BULK: M=1000
- WIRE STRIP LENGTH 1 1/32 <sup>+1/32</sup><sub>-0</sub> (8.7 <sup>+0.8</sup><sub>-0</sub>)



LISTED  
20H3  
E78522



CERTIFIED  
LR31212

PART NUMBER	TAB SIZE	WIRE RANGE AWG	COLOR	MAX. INSUL.	DIMENSIONS in.		
					A ±.02	B ±.01	C ±.02
DNFR18-250F1B	.250 X .032	22-18 (0.3-0.9)	RED	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)
DNFR18-205F1B	.205/.187 X .032	22-18 (0.3-0.9)	RED	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)
DNFR18-206F1B	.205/.187 X .020	22-18 (0.3-0.9)	RED	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)
DNFR14-250F1B	.250 X .032	16-14 (1.3-2.0)	BLUE	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)
DNFR14-205F1B	.205/.187 X .032	16-14 (1.3-2.0)	BLUE	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)
DNFR14-206F1B	.205/.187 X .020	16-14 (1.3-2.0)	BLUE	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)

A41197\_03

03	1/01	KMD		CAD FILE SPEC. WAS N41197AA_PCD_02					TINLEY PARK, ILLINOIS		
02	3/99	JKD		1 1/32 WIRE STRIP LENGTH WAS 9/32	07469						
01	1-95	MC	RLS	UPDATED NOTES AND DIMENSIONS	02895	LCA	DBH	RIGHT ANGLE FULLY INSULATED FEMALE DISCONNECTS .250 X .032, .205/.187 X .032/.020			
00	3-88	DM		RELEASED		LCA	JRB				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY DSM	CHK'D RLS	SCALE NONE	DRAWING NO. A41197