


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	MIN. LOOP * TENSILE lbs. (N)	CROSS SECTION
	MIN. in (mm)	MAX. in (mm)							
HLT2I	.25 (6.4)	1.91 (48.5)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	8.0 (203)	40 (178)	INTERMEDIATE
HLT3I	.25 (6.4)	3.18 (80.6)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	12.0 (305)	40 (178)	INTERMEDIATE

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- * 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

								CAD FILENAME/LAYERS	
								DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS	
								SS_26938_04.PRT	
								PANDUIT CORP. TINLEY PARK, ILLINOIS	
								TAK-TY™ HOOK & LOOP CABLE TIES HLT SERIES	
4	1/8/99	KT		(B) ADDED REF. TO SLOT AND CUT-THRU DIM.	26938	4			
3	10/22/98	KT	HVP	(A) TAK-TY™ WAS VELCRO®	26938	3			
2	01/18/95	KT	HVP	GENERAL REVISIONS (SEE ECN)	26938	2			
1	01/06/95	KT	JAR	GENERAL REVISIONS (SEE ECN)	26938	1			
R	11/28/94	KT	HVP	DRAWING RELEASED	26938	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	
								DRAWN BY KET	MAT'L: POLYETHYLENE HOOK/ NYLON KNIT LOOP
								DATE 11/28/94	SCALE NONE
								CHK'D HVP	DRAWING NO. SS-26938
									DWG SIZE A