



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER		TAB SIZE	WIRE RANGE AWG (mm ²)	DIMENSIONS in		
PREFIX	PKG			A $\pm .015$ (0.4)	B $\pm .010$ (0.3)	C $\pm .010$ (0.3)
D18-188	-C -M	.187 x .020 (4.8 x 0.5)	22-18 (.5-1.5)	.58 (14.7)	.23 (5.8)	.10 (2.5)
*D14-188	-C -M	.187 x .020 (4.8 x 0.5)	16-14 (1.5-2.5)	.58 (14.7)	.23 (5.8)	.10 (2.5)
D18-187	-C -M	.187 x .032 (4.8 x 0.8)	22-18 (.5-1.5)	.58 (14.7)	.23 (5.8)	.10 (2.5)
*D14-187	-C -M	.187 x .032 (4.8 x 0.8)	16-14 (1.5-2.5)	.58 (14.7)	.23 (5.8)	.10 (2.5)



NOTES:

- UL LISTED, UL RECOGNIZED (D14-187 & D14-188 ONLY) AND CSA CERTIFIED FOR:
 - STRANDED COPPER WIRE ONLY
 - 302° F (150° C) MAX TEMP RATING
 - 10 AMP. MAX. (D14-187 & D14-188 ONLY)
- PACKAGE QTY:
 - STD: -C=100
 - BULK: -M=1000
- MATERIAL:
 - STAMPING: .016 (0.41) THK BRASS, TIN PLATED
 - SLEEVE: BRASS, TIN PLATED
- WIRE STRIP LENGTH $9/32 \begin{matrix} +1/32 \\ -0 \end{matrix}$ (7.1 $\begin{matrix} +0.8 \\ -0 \end{matrix}$)
- FIRST INSERTION FORCE: 12 LB (53N) MAX
FIRST WITHDRAWAL FORCE: 12 LB (53N) MAX
6 LB (27N) MIN
- INSTALLATION TOOLS:
 - UL LISTED AND CSA CERTIFIED: CT-100, CT-200, CT-570, CT-1570, CT-2457CH
 - UL RECOGNIZED: CT-100, CT-200, CT-570, CT-1570, CT-2457CH
 - PANDUIT APPROVED: CT-160, CT-260
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS OR mm²



LISTED
20H3
E78522



CERTIFIED
LR31212



RECOGNIZED
E78522

A41305_06

06	1/01	RM		FILESPEC WAS N41305AA_PCD_05						<p>PANDUIT CORP. TINLEY PARK, ILLINOIS</p> <p>NON-INSULATED FEMALE DISCONNECT, SLEEVED BARREL (.188 SERIES)</p>			
05	10/96	TM		ADD 187'S, UPDATED NOTES, FILESPEC WAS NPC_41305_04	05164								
04	3/95	MS	RS	UPDATED NOTES AND DIMENSIONS	03051		LA	KS					
03	1/92	DL	DL	UPDATED FORMAT	00798		LA	KS					
REV	DATE	BY	CHK	DESCRIPTION	ECN #	QA	CUST	PM	APP	DRAWN BY DAW	CHK'D	SCALE NONE	DRAWING NO. A41305