



No. of Positions	DIMENSIONS		
	A	B	C
2	2.00	4.00	N/A
3	4.00	6.00	2.00
4	6.00	8.00	4.00
5	8.00	10.00	6.00
6	10.00	12.00	8.00
7	12.00	14.00	10.00
8	14.00	16.00	12.00
9	16.00	18.00	14.00
10	18.00	20.00	16.00
11	20.00	22.00	18.00
12	22.00	24.00	20.00
13	24.00	26.00	22.00
14	26.00	28.00	24.00
15	28.00	30.00	26.00
16	30.00	32.00	28.00
17	32.00	34.00	30.00
18	34.00	36.00	32.00
19	36.00	38.00	34.00
20	38.00	40.00	36.00
21	40.00	42.00	38.00
22	42.00	44.00	40.00
23	44.00	46.00	42.00
24	46.00	48.00	44.00
25	48.00	50.00	46.00



REV.	ECO	DESCRIPTION	DATE	BY
A	644	INITIAL RELEASE	6/15/2005	TT

SPECIFICATIONS

Current Rating: 1 Amps
 Insulator resistance: 5000 Megohms min.
 Dielectric withstanding: AC 500V
 Operating Temperature: -40° to $+105^{\circ}$ C
 Max Processing Temp: 230° C for 30 seconds
 (260° C for 10 seconds.)
 Contact Material: See part number coding
 Insulator Material: Nylon-6T
 Contact Finish: Gold flash overall



PART NUMBER CODING
 NxPNxx2MAMx-RC

- MOUNTING STYLE**
 P - SURFACE MOUNT W/ GUIDE PINS
 S - SURFACE MOUNT W/O GUIDE PINS
- NUMBER OF POSITIONS**
 (2 - 25)
- CONTACTS**
 P - PHOSPHOR BRONZE
 R - BRASS



ROHS COMPLIANT

Sullins Electronics San Marcos, CA www.SullinsElectronics.com	GENERAL TOLERANCE		SCALE NTS	DRAWN TT	DATE 6/15/2005	DWG. NO. 10495	TITLE 2.00mm HEADER MALE SURFACE MOUNT MALE, 1.5mm INSULATOR	REV. A
	XX. \pm	XXX. \pm						
	X. \pm 0.20	.XXX \pm	SIZE	APPROVE	DATE	PARTS NO. NxPNxx2MAMx-RC	SHEET 1/1	
	.X \pm 0.10	X.* \pm						
.XX \pm 0.05	.X* \pm							